

# Efficient • Hygienic • Environmentally friendly







The unique Paxxo Longopac® system enables smarter waste handling and innovative packaging solutions for a better working environment for professionals worldwide. Longopac is hygienic since the bags are replaced and sealed from the outside – there is **no contact** with the **waste**.

Longopac is based on an extremely thin and strong 3-layer polyethylene material. The bagging material is folded into compact cassettes in specifically developed machines. Longopac gives advantages in the form of efficient and time saving handling, low material consumption and low transport costs.

Longopac is available in many different colors and strengths as well as in Mini, Midi and Maxi size. Longopac is certified to be used in different kinds of handling within: **Odor Control, Biodegradable, Food, ESD, Sterile** as well as with different strengths on the bag cassette.



Color codes

|   |   |   |   |
|---|---|---|---|
|  | 0 |  | 2 |
|  | 1 |  | 4 |
|   |   |  | 5 |
|   |   |  | 6 |

The Longopac bag cassette comes in a variety of strengths and colors.

## HOW IT WORKS

### Step 1

The bag cassette is sealed at one end with a cable tie. Once the "bag" starts to fill up, you just pull it down and new material is drawn from the cassette to make the bag longer.




### Step 2

To make a new bag, pull the material down and seal it at the top with a cable tie.



### Step 3

Add another cable tie above the first one and cut the bag material off between the two cable ties. The entire process takes less than 30 seconds!



## PAXXO AB

Paxxo is a Swedish based packaging company with more than a 35-year history. Our business concept is to manufacture the unique endless bag system Longopac that, thanks to innovative, smarter waste management and packaging solutions, creates a better working environment in many industries. Our success has been possible because our products offer rational handling, a better working environment and low environmental impact.

The unique Longopac system is today sold by certified partners in more than 35 countries.

**Headquarters** for sales, production and R&D is located in Malmö, Sweden. Sales office and distribution warehouse is located in Atlanta, Georgia, USA.

**PAXXO** is certificated in compliance with ISO 9001 and ISO 14 001. We are continuously making our company greener and lowering our products' environmental impact.

**Since 1992** Paxxo has a policy of donating 1 % of profits after taxes to charity.



# Longopac Features & Certifications



## LONGOPAC MINI

Diameter: 357 mm  
Standard: 60 meters long  
Strong: 45 meters long X-  
Strong: 35 meters long Super  
Strong: 22 meters long Mega  
Strong: 20 meters long

## STRENGTHS

- Standard – Mini, Midi, Maxi
- Strong – Mini, Midi, Maxi
- X-Strong – Mini, Maxi
- Super Strong – Mini
- Mega Strong – Mini, Midi

## VERSIONS

### Food

This bag cassette is certified by Normpack (Swedish Code for Food Packaging Materials) for the handling of food and pharma. Food can be packaged for re-use and Pharma for bulk handling.

### Biodegradable

Bio bag cassettes are available for either the disposal or composting of food waste and other organic waste. The Bio bag cassette is produced of organic material that is certified according to EN 13432:2000-12. The material degrades within 6 months at 23°C / 73°F.



## LONGOPAC MIDI

Diameter: 465 mm  
Standard: 85 meters long  
Strong: 70 meters long Mega  
Strong: 25 meters long

## QUALITY

Length and strength measured in Dart Drop is guaranteed. Every roll of Longopac film is Dart Drop tested according to ASTM D-1709. From the reference number, which is printed on every box and on the film, we have traceability all the way to the material batch.

### Odor control

The black odor-control cassette is an extra airtight bag cassette for Longopac Stand. With this cassette you can control odors associated with waste such as diapers.

### ESD

Electro Static Discharge bag cassettes are available in areas that require anti-static material. The surface resistivity value is 1.0E +10 Ohm.



## LONGOPAC MAXI

Diameter: 570 mm  
Standard: 110 meters long  
Strong: 90 meters long X-  
Strong: 70 meters long

## Dart Drop ASTM D-1709, ISO 7765

Paxxo uses the Impact Resistance of Plastic Film by the Free-Falling Dart Method and guarantees the strength measured in Dart Drop for 2 years.

The most common scientific way to test plastic film is by applying the Dart Drop method. The execution of the method can be seen in its entirety on Paxxo's website: [www.paxxo.se/videos/](http://www.paxxo.se/videos/)

### Perforated

This version is only available for Longopac Maxi. The bag cassettes is used for recycling of plastics to enable better result in compactors. There are 6 perforations every 25 cm.

### Pacto

The transparent Pacto material is weldable and can be used for closure and sealing to prevent permeation of environmentally hazardous waste and odors.

### Sterile

Longopac Mini bag cassettes can be gamma sterilized and are packaged in air tight protective bags.



## Longopac® Mini



|   |                                |                  |  |
|---|--------------------------------|------------------|--|
|    | Longopac Mini Transparent      |                  |  |
|   | Standard                       | Item no. 10700   |  |
|   | Strong                         | Item no. 10720   |  |
|   | Extra Strong                   | Item no. 10790   |  |
|   | Food Standard *                | Item no. 10800   |  |
|   | Longopac Sterile 10710 (3 pcs) | Item no.         |  |
|    | Longopac Mini Black            |                  |  |
|   | Standard                       | Item no. 10701   |  |
|   | Strong                         | Item no. 10721   |  |
|   | Extra Strong                   | Item no. 10791   |  |
|   | Mini Odor Control              | Item no. 10001   |  |
|   | (5pcs)                         |                  |  |
|    | Longopac Mini Red              |                  |  |
|   | Standard                       | Item no. 10702   |  |
|   | Strong                         | Item no. 10722   |  |
|  | Longopac Mini Yellow           |                  |  |
|   | Standard                       | Item no. 10704   |  |
|   | Strong                         | Item no. 10724   |  |
|   | Extra Strong                   | Item no. 10794   |  |
|  | Longopac Mini Green            |                  |  |
|   | Standard                       | Item no. 10705   |  |
|   | Strong                         | Item no. 10725   |  |
|  | Longopac Mini Blue             |                  |  |
|   | Standard                       | Item no. 10706   |  |
|   | Strong                         | Item no. 10726   |  |
|   | Food standard *                | Item no. 10806   |  |
|   | Extra Strong                   | Item no. 10796   |  |
|  | Longopac Mini Pink             |                  |  |
|   | Standard                       | Item no. 10707   |  |
|  | Longopac Mini Purple           |                  |  |
|   | Standard                       | Item no. 10708PU |  |









## Longopac® Midi



|   |                           |                |  |
|---|---------------------------|----------------|--|
|      | Longopac Midi Transparent |                |  |
|   | Standard                  | Item no. 10050 |  |
|   | Strong                    | Item no. 10070 |  |
|   | Extra-Strong              | Item no. 10210 |  |
|   | Food Standard *           | Item no. 10090 |  |
|    | Longopac Midi Black       |                |  |
|   | Standard                  | Item no. 10051 |  |
|   | Strong                    | Item no. 10071 |  |
|    | Longopac Midi Red         |                |  |
|   | Standard                  | Item no. 10052 |  |
|   | Strong                    | Item no. 10072 |  |
|    | Longopac Midi Yellow      |                |  |
|   | Standard                  | Item no. 10054 |  |
|   | Strong                    | Item no. 10074 |  |
|    | Longopac Midi Green       |                |  |
|   | Standard                  | Item no. 10055 |  |
|   | Strong                    | Item no. 10075 |  |
|  | Longopac Midi Blue        |                |  |
|   | Standard                  | Item no. 10056 |  |
|   | Food Standard *           | Item no. 10096 |  |
|   | Strong                    | Item no. 10076 |  |
|   | Food Strong *             | Item no. 10016 |  |
|  | Longopac Midi Pink        |                |  |
|   | Standard                  | Item no. 10057 |  |
|   | Strong                    | Item no. 10077 |  |

## Longopac® Maxi



|   |                           |                  |  |
|---|---------------------------|------------------|--|
|    | Longopac Maxi Transparent |                  |  |
|   | Standard                  | Item no. 10170   |  |
|   | Standard (perf.)          | Item no. 10160   |  |
|   | Strong                    | Item no. 10290   |  |
|   | Extra Strong              | Item no. 10400   |  |
|   | Food Standard **          | Item no. 10450   |  |
|   | Food Standard *           | Item no. 10300   |  |
|   | Ultra Lean (perf.)        | Item no. 10960   |  |
|   | Ultra Lean                | Item no. 10990   |  |
|    | Longopac Maxi Black       |                  |  |
|   | Standard                  | Item no. 10171   |  |
|   | Strong                    | Item no. 10291   |  |
|   | Extra Strong              | Item no. 10401   |  |
|    | Longopac Maxi Red         |                  |  |
|   | Standard                  | Item no. 10172   |  |
|   | Strong                    | Item no. 10292   |  |
|  | Longopac Maxi Yellow      |                  |  |
|   | Standard                  | Item no. 10174   |  |
|   | Strong                    | Item no. 10294   |  |
|  | Longopac Maxi Green       |                  |  |
|   | Standard                  | Item no. 10175   |  |
|   | Strong                    | Item no. 10295   |  |
|  | Longopac Maxi Blue        |                  |  |
|   | Standard                  | Item no. 10176   |  |
|   | Strong                    | Item no. 10296   |  |
|   | Food Standard **          | Item no. 10456   |  |
|   | Food Standard *           | Item no. 10306   |  |
|  | Longopac Maxi Pink        |                  |  |
|   | Standard                  | Item no. 10177   |  |
|  | Longopac Maxi Purple      |                  |  |
|   | Standard                  | Item no. 10178PU |  |

Upon request and volume, other colours can be produced in all sizes.

\* = with metal detectable clips  
\*\* = with blue clips

# Longopac® ESD



- Longopac Mini ESD  
 Standard                      Item no. 10507  
 Strong ESD                      Item no. 10647
- Longopac Midi ESD  
 Strong ESD                      Item no. 10107
- Longopac Maxi ESD  
 Standard ESD                      Item no. 10437  
 Strong ESD                      Item no. 10367

# Longopac® Bio



- Longopac Mini Biodegradable  
 Bio HC                              Item no. 10610
- Longopac Mini Biodegradable  
 Bio IC                                Item no. 10650
- Longopac Midi Biodegradable  
 Bio IC                                Item no. 10110
- Longopac Maxi Biodegradable  
 Bio IC                                Item no. 10320

Longopac is available in several choices, below shows the length of most of the cassettes.

| Length | Standard | Strong | Extra Strong | ESD  | Bio         | Sterile |
|--------|----------|--------|--------------|------|-------------|---------|
| Mini   | 60 m     | 45 m   | 35 m         | 45 m | 40 m & 45 m | 60 m    |
| Midi   | 85 m     | 70 m   | 40 m         | 70 m | 70 m        | -       |
| Maxi   | 110 m    | 90 m   | 70 m         | 80 m | 80 m        | -       |

*All clips are delivered black except where specified as others.*

*Upon request and volume, other colours can be produced in all sizes.*



recycling

[easirecycling.co.nz](http://easirecycling.co.nz)

Freephone 0800 342 3177



Easi Recycling NZ Limited.  
Freephone: 0800 342 3177  
E: [info@easirecycling.co.nz](mailto:info@easirecycling.co.nz)  
[www.easirecycling.co.nz](http://www.easirecycling.co.nz)